


STAINLESS STEEL DISTRIBUTION MANIFOLDS

Application

The 220A2-I3 te-sa pre-assembled distribution manifolds are designed for the distribution and regulation of heat transfer fluid in heating and conditioning systems.

Made of stainless steel material, they are ideally suited to radiant panel heating systems, but also for traditional radiator heating systems with condensing boilers. The manifold when completed with its preformed insulation is usable for conditioning systems. The particular design of the manifold features a great flow section with reduced pressure drops and consequently lower energy consumption in the circulator pumps. The big flow section of these manifolds permits to the water to reduce its speed, with the result to have very low noises produced. Beautiful to the eye. it is strong, reliable and corrosion resistant in the ordinary applications



Configuration and available sizes

Pre-assembled on brackets, it is a distribution manifold with 3/4" M Eurocone loop connections with centre distance 50 mm, and it is composed by supply manifold with micrometric regulating lockshield valves, return manifold with built-in interception valves, with maneuver handles, that are predisposed for assembly of electrothermal actuators. The barrels are completed with end plugs, orientable fill and drain valves with 3/4" hose connection and automatic air vent valves. At the manifold are combined full port ball valves with tailpiece flat seat that are equipped with thermometer for the prompt control of the water temperatures in supply and return. The manifold is packaged in carton box with labels included to identify the circuits connected.

1" inlet connection

220A2-06-02I3	2 Loops
220A2-06-03I3	3 Loops
220A2-06-04I3	4 Loops
220A2-06-05I3	5 Loops
220A2-06-06I3	6 Loops
220A2-06-07I3	7 Loops
220A2-06-08I3	8 Loops
220A2-06-09I3	9 Loops
220A2-06-10I3	10 Loops
220A2-06-11I3	11 Loops
220A2-06-12I3	12 Loops

1-1/4" inlet connection


220A2-07-02I3	2 Loops
220A2-07-03I3	3 Loops
220A2-07-04I3	4 Loops
220A2-07-05I3	5 Loops
220A2-07-06I3	6 Loops
220A2-07-07I3	7 Loops
220A2-07-08I3	8 Loops
220A2-07-09I3	9 Loops
220A2-07-10I3	10 Loops
220A2-07-11I3	11 Loops
220A2-07-12I3	12 Loops



Technical data

- Manifold barrel made stainless steel EN 1.4301-AISI304 UNI-EN 10088
- Manifold components made of brass alloy UNI-EN 12164 CW614N and UNI-EN 12165 CW617N
- Automatic air vent valves and fill/drain valves mounted on the manifold bars
- Full port ball valves 1" with self-sealing tailpiece flat seat and equipped with thermometer
- Supply manifold with micrometric lockshields to be set with 5 mm wrench
- Return manifold equipped with intercepting valves with ABS handles, suitable for the installation of electrothermal actuators with M30x1,5 swivel nut connection
- Thermometer with needle range 0 ÷ 80 °C
- Maximum Operating Pressure 10 bar
- Operating Temperature 0 ÷ 85 °C
- Maximum Test Pressure 16 bar
- Maximum glycol percentage 30%
- KV factors in full open conditions: Supply manifold 1" KV=4,42 ; Return manifold 1" KV=2,8 ; Supply manifold 1-1/4" KV=4,58 ; Return manifold 1-1/4" KV=3,55 ; Supply + Return 1" KV=2,36 ; Supply + Return 1-1/4" KV=2,80 ;
- Available KV factors of the regulating lockshield according to the number of opening turns

Dimensions



Art.	A	B	C	D	E	F	G	H	I	L
220A2-06-02I3	1"	3/4"	50	32	32	64	95	320	206	270
220A2-06-03I3	1"	3/4"	50	32	32	64	95	320	206	320
220A2-06-04I3	1"	3/4"	50	32	32	64	95	320	206	370
220A2-06-05I3	1"	3/4"	50	32	32	64	95	320	206	420
220A2-06-06I3	1"	3/4"	50	32	32	64	95	320	206	470
220A2-06-07I3	1"	3/4"	50	32	32	64	95	320	206	520
220A2-06-08I3	1"	3/4"	50	32	32	64	95	320	206	570
220A2-06-09I3	1"	3/4"	50	32	32	64	95	320	206	620
220A2-06-10I3	1"	3/4"	50	32	32	64	95	320	206	670
220A2-06-11I3	1"	3/4"	50	32	32	64	95	320	206	720
220A2-06-12I3	1"	3/4"	50	32	32	64	95	320	206	770

Art.	A	B	C	D	E	F	G	H	I	L
220A2-07-02I3	1 1/4"	3/4"	50	32	36	69	104	320	206	280
220A2-07-03I3	1 1/4"	3/4"	50	32	36	69	104	320	206	330
220A2-07-04I3	1 1/4"	3/4"	50	32	36	69	104	320	206	380
220A2-07-05I3	1 1/4"	3/4"	50	32	36	69	104	320	206	430
220A2-07-06I3	1 1/4"	3/4"	50	32	36	69	104	320	206	480
220A2-07-07I3	1 1/4"	3/4"	50	32	36	69	104	320	206	530
220A2-07-08I3	1 1/4"	3/4"	50	32	36	69	104	320	206	580
220A2-07-09I3	1 1/4"	3/4"	50	32	36	69	104	320	206	630
220A2-07-10I3	1 1/4"	3/4"	50	32	36	69	104	320	206	680
220A2-07-11I3	1 1/4"	3/4"	50	32	36	69	104	320	206	730
220A2-07-12I3	1 1/4"	3/4"	50	32	36	69	104	320	206	780

Installation of the electrothermal actuators 116T

The installation of the electrothermal actuators 116T is very easy and quickly. After removing the maneuver handle, screw completely by hand the plastic adapter at the thread M30x1,5 of the bonnet. The actuator is connected to the adapter with slight pressure, and can be oriented a little by turning it. The electrothermal actuators are supplied with the stem in middle position. At starting, to totally close the interception valve of the manifold, it is necessary connect the actuator at the electrical power supply for some minutes to open it completely. When the electrical power is removed, the actuator totally closes. The actuators 116T series are Normally Closed type, then with electrical supply they open, while without electrical supply they close.



Accessories



208 – 216T – 217T Compression fittings with nut threaded 3/4" Eurocone, to connect copper pipes, polyethylene pipes and multilayer pipes at the manifolds. Available for the main commercial sizes of pipes.



650A Pre-formed insulation shells for manifolds, consisting of two half-shells (front and back).
Material: PE-X closed-cell foam.
Available sizes 1" and 1-1/4".



116T Electrothermal actuator normally closed with easy and fast connection. For bonnets M30x1,5. Available with and without end switch (two or four wires) in the voltages 230V and 24V.



211N11 Full painted metal cabinet with key on door for embedded installation.
Dimensions: 45 cm Height, 11÷15 cm Depth, 40-60-80-100-120 cm Width.